

S E R V I C E N O T E

SUPERSEDES: None

16117B Low-Noise Test leads**Design of Interlock Cable has been changed****Situation:**

The 16117B consists of three cable assemblies (BNC, Triaxial and Interlock) and the plastic holders which hold three cables. The Interlock Cable (P/N 16117-61603) has a stopper so that the plastic holders can hold it.

Solution:

So far, this stopper was made by the cable tie. But recently its design has been changed for improving durability. The new stopper is attached on the cable more tightly by being covered with the heat shrinkable tube. The method of attaching the cable to the plastic holders is same as before. Just put the stopper covered with the tube between the plastic holders.

DATE: February 1995

ADMINISTRATIVE INFORMATION

SERVICE NOTE CLASSIFICATION:

INFORMATION ONLY

AUTHOR:

YM

ENTITY:

3355

ADDITIONAL INFORMATION:

