

N7976A-02

Modification Recommended Service Note

Supersedes:
NONE

N7976A Advanced Power System – DC Power Supply, 120 V, 16.7 A, 2000 W

Serial Numbers: MY54410157

The Problem – Non-RoHS compliance due to two leaded resistors.

Parts Required:

P/N	Description	Qty.
5067-5570	Tested PCA Main Series Conn PBV 60V	1
5067-5575	Tested PCA Slave Series Conn PBV 60V	1

ADMINISTRATIVE INFORMATION

ACTION	<input type="checkbox"/> ON SPECIFIED FAILURE	STANDARDS			
CATEGORY:	<input checked="" type="checkbox"/> AGREEABLE TIME	LABOR:	1.5 Hours		
LOCATION	<input type="checkbox"/> CUSTOMER INSTALLABLE	SERVICE:	<input type="checkbox"/> RETURN	USED	<input type="checkbox"/> RETURN
CATEGORY:	<input type="checkbox"/> ON-SITE (active On-site contract required)	INVENTORY:	<input checked="" type="checkbox"/> SCRAP	PARTS:	<input checked="" type="checkbox"/> SCRAP
	<input checked="" type="checkbox"/> SERVICE CENTER		<input type="checkbox"/> SEE TEXT		<input type="checkbox"/> SEE TEXT
	<input type="checkbox"/> CHANNEL PARTNERS				
AVAILABILITY:	PRODUCT'S SUPPORT LIFE	NO CHARGE AVAILABLE UNTIL:	1 st December 2019		
	<input checked="" type="checkbox"/> Calibration Required	PRODUCT LINE:	SP		
	<input type="checkbox"/> Calibration NOT Required	AUTHOR:	KHEW		

ADDITIONAL INFORMATION:

Situation:

N7976A with serial number listed in Table 1 was loaded with 2 pcs of leaded resistors. While this does not impact on the product functionality and long-term reliability; it is non-compliant to RoHS as N7976A is declared as RoHS compliant unit.

Solution/Action:

The impacted unit can be enhanced to RoHS Compliance by sending back to Keysight Service Center for Main (5067-5570) and Slave (5067-5575) PCA board replacement. Kindly contact Keysight Technologies Customer Contact Center at www.keysight.com/find/contactus.

Revision History:

Date	Service Note Revision	Author	Reason for Change
14 Nov 2018	01	Khew	As Published